


Flow-Thru Troffers allow HEPA or ULPA filtered air to flow through the fixture and into the clean room.

Flow-Thru Troffers feature four lamps, sealed housings and a white powdercoated finish.


A drop-down acrylic eggcrate grille with an anodized aluminum frame permits removal of the lamps and ballast from roomside.

Standard ballasts are 120-277 Multi-voltage, T8 electronic for use with (4) medium bi-pin lamps. The ballast is mounted inside the housing and is removable from roomside.

All electrical components are UL listed.



Exploded View of SAM Unit and Flow-Thru Troffer



Shown with Optional Power Cord

Ordering Information		
Part No.	Description	Amps
148500	2' x 4', 120-277 Multi-Voltage, 4 Lamp	*1
148510	2' x 2', 120-277 Multi-Voltage, 4 Lamp	*2
703902	Optional Power Cord (110-120 Volt Only)	
703754	Replacement Ballast 120V-277V Multi-Voltage	
	Note: All Multi-Voltage ballasts are 50/60 hz. Fluorescent lamp tubes not included.	

\*1. 120V = .93 amps, 277V = .40 amps

\*2. 120V = .94 amps, 277V = .40 amps

Shipping Information	
Part No.	Weight
148500	31 lbs. (14 kg.)
148510	28 lbs. (13 kg.)

